



Product Portfolio Guide

Summer 2026



Tech that's yesterday's thinking **or future driven?**

From enhancements to our in-demand Omega AI to a new essential line featuring two new BTEs, Starkey is setting the speed of innovation with technology that lets you fit AI-powered performance on every patient—all using the same fitting software and app.

ASK MORE from your technology partner

OMEGA^{AI}

Tech Tier/Channels/Bands

24 / 20 / 16

AURACAST

CROS COMPATIBLE



mRIC R



RIC RT



RIC 312



CIC



ITC R



ITE R



- Waterproof*
- Rechargeable
- LED Status Indicator Light
- Wireless
- Telecoil

*Up to 1m.

Available Colors

- Standard Colors**
- White
 - Tech Black
 - Graphite Gray
 - Silver
 - Chestnut
 - Caramel
 - Beige

- Custom Colors**
- Faceplate Colors**
- Pink
 - Light Brown
 - Medium Brown
 - Chestnut
 - Dark Brown
 - Black

- Shell Colors**
- Clear
 - Pink
 - Light Brown
 - Blue/Red
 - Black

SnapFit 2.0 Stock and Custom Cased Receivers



Comfort Bud Open
5 mm, 6 mm, 7 mm,
9 mm, 11 mm



Comfort Bud Occluded
4 mm, 5 mm, 6 mm,
7 mm, 9 mm, 11 mm



Power Dome
8-10 mm, 10-12 mm,
12-14 mm




Custom Cased Receiver
Custom shell with
embedded receiver



Stock Silicone Helix
RIC Earmold






Stock Hollow
Silicone RIC Earmold



Stock Silicone
RIC Earmold

Fitting Ranges



Visit StarkeyPro.com/OmegaAI for full technical data sheets.



Engineered with our industry-leading AI, our G3 Gen AI Neuro Processor, and the world's first DNN-powered directionality system, DNN 360, Omega AI is Starkey's most advanced hearing technology yet. It's designed to come closer to restoring the normal sense of hearing than any hearing technology before it.

For more Omega AI details,
visit StarkeyPro.com/OmegaAI



OMEGA ^{AI}				
Tech Tiers Channels Bands				
Edge Mode+				
Automatic & User Control Personalization <i>App Control</i>		24	20	16
Speech Optimization				
Consonant Brightness <i>Voice AI*</i>		Maximum	Mild	Mild
Sound Manager				
DNN 360	DNN Directionality**			
	DNN Spatial Awareness**			
	Quiet	Maximum expansion	Moderate expansion	Mild expansion
	Machine Noise Reduction	Up to 22 dB of reduction	Up to 12 dB of reduction	Up to 7 dB of reduction
	Speech in Noise Reduction	Up to 22 dB of reduction	Up to 10 dB of reduction	Up to 8 dB of reduction
	Transient Noise Reduction	Up to 15 dB of reduction	Up to 9 dB of reduction	Up to 6 dB of reduction
Wind Reduction		Up to 35 dB of reduction	Up to 19 dB of reduction	Up to 10 dB of reduction
Additional Key Features				
Gen AI Smart Assistant & TeleHear AI Translate				
<i>ALL NEW</i> Push-to-talk Transcribe				
Multiflex Tinnitus Pro				
<i>ALL NEW</i> Auracast™ assistant				
<i>ALL NEW</i> Google Fast Pair™				
Smart Assistant & 2-Way Audio				
Hearing Health & Activity Tracking				
Fall Alert & Balance Assessment				
Reminders & Self Check				
Tap Control				
TeleHear full remote fit				
REM Target Match				
Demo Stream				

Wireless Accessories

ALL NEW



StarLink Edge
LE Adapter
Part No. P00018678



StarLink Edge
Remote Microphone
Part No. P00004321



StarLink Edge
Table Microphone
Part No. P00004326



StarLink Edge
TV Streamer
Part No. P00004315



StarLink
Remote Control 2.0
Part No. P00002347

AURACAST

Charging Solutions

All chargers include
Turbo Charge

Serve as a charging station and carrying case for your rechargeable hearing aids.



StarLink Premium
Charger 3.0
w/ onboard battery

- RIC RT



StarLink Premium
Charger 2.0
w/ onboard battery

- mRIC R



StarLink Premium
Custom Charger 2.0
w/ onboard battery

- ITC/ITE R

StarLink Charger 3.0

- RIC RT


StarLink Charger 2.0

- mRIC R

StarLink Custom Charger 2.0

- ITC/ITE R


Compatible Apps



My Starkey



Edge Mode+



Hear Share



Scan QR code
to check phone
compatibility



Download on the
App Store



GET IT ON
Google Play

Tech Tier/Channels/Bands

24 / 20* / 16*



IIC NW



CIC NW



CIC R NW



Waterproof**
Rechargeable

For more product details,
visit StarkeyPro.com



Faceplate Colors

- Pink
- Light Brown
- Medium Brown
- Chestnut*
- Dark Brown
- Black

Shell Colors

(IIC only available in Black)

- Clear
- Pink
- Light Brown
- Blue/Red
- Black

Charging Solutions

Both chargers include
Turbo Charge





StarLink Premium Custom Charger 2.0
w/ onboard battery

• CIC R NW

StarLink Custom Charger 2.0

• CIC R NW

Fitting Ranges



Visit StarkeyPro.com for full technical data sheets.

Tech Tiers | Channels | Bands

24

20*

16*

Edge Mode+ (CIC styles only)

User Control



Speech Optimization

Consonant Brightness

Maximum

Mild

Mild

Sound Manager

Quiet



Maximum expansion

Moderate expansion

Mild expansion

Machine Noise Reduction



Up to 22 dB of reduction

Up to 12 dB of reduction

Up to 7 dB of reduction

Speech in Noise Reduction



Up to 22 dB of reduction

Up to 10 dB of reduction

Up to 8 dB of reduction

Transient Noise Reduction



Up to 15 dB of reduction

Up to 9 dB of reduction

Up to 6 dB of reduction

Wind Reduction



Up to 35 dB of reduction

Up to 19 dB of reduction

Up to 10 dB of reduction

Additional Key Features

Multiflex Tinnitus Pro
with new tinnitus maskers



REM Target Match



Waterproof**



Powered by our industry-leading Neuro Sound Technology, Starkey Signature Series delivers the size, performance and personalized fit that patients can only get from you.

*CIC styles only. **Up to 1m. Rechargeable style only.

Quality in... quality out

Your professional expertise is critical when selecting the best solution for a patient. Many factors and considerations come into play when determining if a patient is a custom hearing aid candidate, including:

- Audiogram
- Dexterity
- Ear anatomy and history
- Lifestyle

Ultimately, **the patient has come to you** to weigh all considerations—physical, audiological and lifestyle—and recommend a solution that delivers both success and satisfaction.

A **superior custom product fitting starts with a high quality ear impression**. Making a perfect impression requires proper technique, attention to detail, and repetition.

As the custom hearing aid experts, we know a thing or two about making accurate, precision-tested impressions —and how good impressions can also be used to make earmolds, custom cases, hearing protection solutions and more.



Scan the QR code or go to StarkeyPro.com for support materials, how-to videos, and more.

Developed with help from Starkey's most experienced impression takers, these tools provide best practice tips perfected from shooting thousands of impressions in our Center for Excellence.

EDGE^{AI}

Tech Tier/Channels/Bands

24 / 20 / 16

AURACAST

CROS COMPATIBLE



mRIC R



RIC RT



RIC 312



- Waterproof*
- Rechargeable
- Wireless
- Telecoil

*Up to 1m.

Available Colors

Standard Colors

- White
- Tech Black
- Graphite Gray
- Silver
- Chestnut
- Caramel
- Beige

SnapFit 2.0 Stock and Custom Cased Receivers



Comfort Bud Open

5 mm, 6 mm, 7 mm,
9 mm, 11 mm



Comfort Bud Occluded

4 mm, 5 mm, 6 mm,
7 mm, 9 mm, 11 mm



Power Dome

8-10 mm, 10-12 mm,
12-14 mm



Custom Cased Receiver

Custom shell with
embedded receiver



Stock Silicone Helix
RIC Earmold





Stock Hollow
Silicone RIC Earmold



Stock Silicone
RIC Earmold

Fitting Ranges



Visit StarkeyPro.com/EdgeAI for full technical data sheets.



Powered by the G2 Neuro Processor with the neural processing unit (NPU) integrated into the chip, and Bluetooth® Low Energy (LE) Audio streaming protocol, Starkey's Edge AI advanced processing is able to provide so much more than all-day battery life and waterproof protection – allowing patients to live easier, more connected lives.

For more Edge AI details,
visit StarkeyPro.com/EdgeAI



EDGE^{AI}

Tech Tiers | Channels | Bands

24

20

16

Edge Mode+			
Automatic	●	○	○
User Control	●	○	○
Personalization	●	●	○
App Control	●	●	●
Speech Optimization			
Consonant Brightness	●	●	●
Voice AI*	●	○	○
Sound Manager			
Quiet 	Maximum expansion ●●●	Moderate expansion ●●○	Mild expansion ●○○
Machine Noise Reduction 	Up to 22 dB of reduction ●●●●	Up to 12 dB of reduction ●●○○	Up to 7 dB of reduction ●○○○
Speech in Noise Reduction 	Up to 22 dB of reduction ●●●●	Up to 10 dB of reduction ●●○○	Up to 8 dB of reduction ●○○○
Transient Noise Reduction 	Up to 15 dB of reduction ●●●●	Up to 9 dB of reduction ●●○○	Up to 6 dB of reduction ●○○○
Wind Reduction 	Up to 35 dB of reduction ●●●●	Up to 19 dB of reduction ●●○○	Up to 10 dB of reduction ●○○○
Additional Key Features			
Translate	●	○	○
Transcribe	●	●	○
Multiflex Tinnitus Pro	●	●	○
ALL NEW Auracast™ assistant	●	●	●
Smart Assistant & Find My Hearing Aids	●	●	●
2-Way Audio	●	●	●
Hearing Health & Activity Tracking	●	●	●
Fall Alert & Balance Assessment	●	●	●
Reminders & Self Check	●	●	●
Tap Control	●	●	●
TeleHear full remote fit	●	●	●
REM Target Match	●	●	●
Demo Stream	●	●	●
Waterproof up to 1m**	●	●	●

Wireless Accessories

ALL NEW



StarLink Edge
LE Adapter
Part No. P00018678



StarLink Edge
Remote Microphone
Part No. P00004321



StarLink Edge
Table Microphone
Part No. P00004326



StarLink Edge
TV Streamer
Part No. P00004315

AURACAST



StarLink
Remote Control 2.0
Part No. P00002347

Charging Solutions

All chargers include
Turbo Charge



StarLink Premium
Charger 3.0
w/ onboard battery
• RIC RT

StarLink Charger 3.0
• RIC RT



StarLink Premium
Charger 2.0
w/ onboard battery
• mRIC R


StarLink Charger 2.0
• mRIC R





StarLink Premium
Custom Charger 2.0
w/ onboard battery
• ITC/ITE R

StarLink
Custom Charger 2.0
• ITC/ITE R

Compatible Apps



My Starkey



Hear Share



Scan QR code
to check phone
compatibility



INTRODUCING

G SERIES^{AI}

Tech Tier/Channels/Bands

24* / 20* / 16* / 12 / 10



RIC R



RIC 312



P BTE 13



UP BTE 13



- Waterproof**
- Rechargeable
- Wireless
- Telecoil

*BTE styles only.
**Up to 1m.

Available Colors

Standard Colors

- Graphite Gray
- Silver
- Chestnut
- Beige

SnapFit 2.0 Stock and Custom Cased Receivers



Comfort Bud Open
5 mm, 6 mm, 7 mm,
9 mm, 11 mm



Comfort Bud Occluded
4 mm, 5 mm, 6 mm,
7 mm, 9 mm, 11 mm



Power Dome
8-10 mm, 10-12 mm,
12-14 mm



Custom Cased Receiver
Custom shell with
embedded receiver



Stock Silicone Helix
RIC Earmold



Stock Hollow
Silicone RIC Earmold







Stock Silicone
RIC Earmold



Stock Thin Tube Solution

Fitting Ranges



Visit [StarkeyPro.com](https://www.starkeypro.com) for full technical data sheets.



Powered by our industry-leading Neuro Sound Technology, G Series AI offers an easy, affordable, and immediate way to improve patient hearing and reconnect them with the world around them.

For more product details,
visit [StarkeyPro.com](https://www.starkeypro.com)



Speech Optimization

Ear-to-Ear Technology
Frequency Lowering



Sound Manager

Directionality



Adaptive Adaptive Adaptive Dynamic Dynamic


Transient Noise



Quiet



Machine Noise Reduction



Speech in Noise Reduction



Wind Reduction



Additional Key Features

Edge Mode+



Reminders



Multiflex Tinnitus Technology

(white, pink, & ocean noise only) (white, pink, & ocean noise only) (white noise only)

Find My Hearing Aids



Self Check



TeleHear full remote fit



REM Target Match



Apple Watch Controls**



Wireless Accessories



StarLink
Remote Control 2.0
Part No. P00002347



StarLink Mini
Remote Microphone
Part No. 43121-000



StarLink
Remote Microphone +
Part No. 43120-000



StarLink
Table Microphone
Part No. 43123-610



StarLink
TV Streamer
Part No. 43119-000

Charging Solutions

All chargers include
Turbo Charge




StarLink Premium Charger 3.0
w/ onboard battery
• RIC R



StarLink Charger 3.0
• RIC R

Compatible Apps



My Starkey



Scan QR code to check
phone compatibility



My Starkey App

Easy as it gets. Powerful as you need.



My Starkey

Focus on benefits

Omega AI, Edge AI, and G Series AI wireless hearing aids can connect via Bluetooth® technology to the My Starkey app.

- **Hear better anywhere**

Make instant adjustments for clearer speech and reduced noise – even in the toughest listening environments.

- **Get tips, tools, and resources**

Adapt to hearing aids faster with quick how-to's, tips, and videos. All tailored for where the hearing aid wearer is on their hearing journey.

- **Monitor health and wellness***


Monitor daily hearing and physical activity to help stay healthy. Set and achieve goals for hearing, steps, exercise, and beyond.

- **All from the palm of your hand or wrist**

Change programs and adjust volume quickly and easily on a compatible Apple Watch. Visit the Learn section within My Starkey for installation instructions.

How to download

1. Open the **App Store**  on Apple devices or **Google Play**  on Android devices.
2. In the search box, type  **My Starkey**.
3. Tap **GET** on Apple devices or **INSTALL** on Android devices. This will download the app to the compatible device.



A new dimension in connectivity

All-new **Auracast™** assistant and **Google Fast Pair™** technology make connectivity so convenient, it's automatic.

ALL NEW


*To learn more, visit
StarkeyPro.com*



*Compatible with Omega AI and Edge AI products only.

Other Apps


Enhance the capabilities of our hearing aids and simplify daily life with our lineup of popular hearing apps.



SoundCheck Live

Helps anyone gain awareness of noise exposure and the importance of protecting hearing by:

- Measuring sound levels around them using the built-in sound level meter.
- Learning about environmental noise's impact on hearing and how hearing protection devices like SoundGear can help.



Hear Share

Works with My Starkey app to allow wearers of Omega AI and Edge AI to:

- Share information about hearing aid usage, social and physical activity progress, safety, and more—with the people they choose.
- Provide peace of mind for patients and their caregivers.



Hearing Protection

Be your community's full-service hearing care expert by offering hearing protection products from SoundGear. SoundGear products come in a variety of electronic and non-electronic solutions.



Electronic Solutions



PHANTOM Custom Fit Electronic

World's first custom, rechargeable, and Bluetooth® compatible hearing aid and protection device. Up to 30 dB gain.



SHIELD

Small, light and ready to take everywhere delivering dynamic digital hearing protection anytime you need it.

 **93 dB** | Part No. P00001867

 **80 dB** | Part No. P00001866



RACING RECEIVERS

Custom design allows for maximum comfort and durability for amateur and professional drivers to experience quality one-way listening communication.

	Top Seller	
	Phantom	Shield
Fit	Custom	Universal
Rechargeable	Yes	No
NRR	22 dB	26 dB
Warranty	1 year	1 year
Color Options	●	
Lanyard	●	●
Bluetooth	●	
Digital Modes	●	

Non-electronic Solutions



Filtered Earplug HS Silicone

Referred to as musician or industrial earplugs, these earplugs attenuate across all frequencies.



Solid Earplug HS Silicone

Outstanding noise protection in a variety of recreational and occupational environments.



High-Frequency Noise Filter HS Silicone

Referred to as "Hocks", these earplugs contain a patented acoustical chamber and filter that attenuate sound to appropriate levels.

Additional SoundGear earmolds:

Newscaster/Teleprompter mold
Digital SLS/HS Silicone

Bluetooth mold
HS Silicone

Pilot headset with boom
Digital SLS

Sleeping earplug
HS Silicone

Anesthesiologist mold
Digital SLS

Swim earplug
Floatable Silicone

**For a full selection of custom options,
please contact Customer Service.**

Personal Audio

For musicians, music aficionados, or professionals looking for a custom audio solution, Starkey has options to maximize their hearing experience.

Tunz Duo S | Tunz Duo | Tunz Solo

Additional Items

**SoundGear Custom Charger
for Phantom devices**
Part No. 43059-610

Replacement Tri-flanges for Shield
Size 1: P00009811 (4pk)
Size 2: P00009812 (4pk)

Foam Buds Assorted for Shield
Part No. P00009810 (6pk)

Replacement Filters
Filtered earplug: 10 dB, 17 dB, 26 dB,
Impulse, Total block **High-Frequency
(Hock):** Part No. 50293-000

SoundGear Black Lanyard
Variety of lengths available
SoundGear Zipper Pouch
Part No. 91289-007

Hearing Aid Earmolds

As the leader in customization, Starkey understands offering your patients an expansive portfolio of hearing care solutions specific to their needs is key.



Hear better. Live better.

Material Options

Digital SLS Acrylic	• RIC • BTE & Thin Tube • Specialty*	• One color	Most Rigid
			90 Shore
High Strength Silicone 60	• RIC • BTE & Thin Tube • Specialty*	• Swirl - max. 3 colors • Glitter option	60 Shore
High Strength Silicone 40	• RIC • BTE & Thin Tube • Specialty*	• Swirl - max. 3 colors • Glitter option	40 Shore
Floatable Silicone	• Swim Earplug (SoundGear only)	• Swirl - max. 3 colors	25 Shore
			Softest

Venting Guide

This guide is applicable for all hearing aid earmolds.**
Vent size is limited by ear anatomy.

Vent Name	Approximate Size
Small	1.2 mm
Medium	1.8 mm
Large	2.55 mm
Select-A-Vent	3.37 mm
Extra Large	As large as canal allows

Specialty Solutions



HA Listening Test Mold

Digital SLS
A shell or skeleton style earmold with a tubing attachment for listening to ITE/ITC/CIC/RIC style and BTE hearing aids for listen checks.




Stent Mold

Digital SLS
A hollowed shell of canal style earmold to hold the ear canal open.


RIC Solutions

RIC Earmolds Digital SLS / HS Silicone 60 / HS Silicone 40

Available for both SnapFit 2.0 and SnapFit Receivers



Custom Cased or Absolute Power (AP) Receivers Digital SLS



Color Options*


Our earmolds come in a variety of color options. Some colors appear differently in certain color families based on material type.
Swirl combinations are also available using up to three colors.




Pro tip: Adding White as one of the three colors within a color swirl combination will help separate and make the other color choices "pop." Avoid combining light colors with "clear" or combining similar colors.

BTE Solutions

Thin Tube Earmolds Digital SLS / HS Silicone 60 / HS Silicone 40



Traditional Earmolds Digital SLS / HS Silicone 60 / HS Silicone 40



Color combinations to avoid: "Light" colors combined in Swirl or "Light" colors combined with "Clear". Similar colors combined in Swirl combination will help separate and make the other color choices "pop."

Business Solutions

In addition to our industry-leading products, we offer a full suite of business solutions designed to keep your practice thriving.



Hear better. Live better.

Business Equipment

State-of-the-art diagnostic equipment is essential to providing the best patient experience at your practice. With the help of our Business Equipment Services, it's never been easier to find and maintain the right solutions for all your testing and fitting needs— all in one place. **Equipment includes (but not limited to):**

- Audiometers
- Tympanometers
- Fitting equipment
- Combination units
- Video otoscopes
- Supplies
- Sound rooms/enclosures

All Make Repair

Our All Make Repair department services hearing aids that are damaged and out of manufacturer's warranty. This even includes hearing aids by manufacturers no longer in business. **Our team is here to help with the following:**

- All Make Repair estimates
- Reconditioned aids orders
- Miscellaneous parts and accessory orders
- Analog aids
- Body aids
- Bone conduction aids
- All Make Salvage Program
- Hearing Aid Recycle Program

Batteries

Not only does every battery purchase deliver a positive jolt to your bottom line, each visit to your office for batteries is one more chance to build loyalty and generate referrals from your patients.

- **Drive retention**
Returning patients are more likely to purchase upgrades, warranties and accessories from you due to the ongoing care and service that you provide.
- **Build loyalty**
Superior aftercare will lock in your existing patients rather than allowing them to go to your competition for their future hearing healthcare needs.
- **Boost prospects**
Use battery promotions to attract new patients to your practice.
- **Protect patients' investment**
High quality batteries protect your patient's investment and enhance your patient/provider relationship.
- **Make the right selection**
Choose from long-lasting customized or branded batteries, depending on your business goals.

Hearing is Our Concern

Manufacturer according to Health Canada: Starkey Labs Canada Co. 2476 Argentia Road Suite 301, Mississauga, ON L5N 6M1; www.starkeycanada.ca.

Starkey logo, Starkey, TeleHear, Starkey Edge, Starkey G Series, Edge Mode, Multiflex Tinnitus, StarLink, Starkey Signature Series, SoundGear Shield, Omega, Sound [+checkmark], Hear Share, SoundGear logo, SoundGear, Phantom, Hearing is Our Concern, Hear better. Live better., Neuro Processor, DNN 360 and Tunz are trademarks of Starkey Laboratories, Inc.

The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. The Auracast™ word mark and logos are trademarks owned by the Bluetooth SIG. Any use of such marks by Starkey is under license. Other trademarks and trade names are those of their respective owners.

Apple Watch and App Store are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. "Made for iPod," "Made for iPhone" and "Made for iPad" mean that an electronic accessory has been designed to connect specifically to iPod, iPhone, or iPad, respectively, and has been certified by the developer to meet Apple performance standards. Apple is not responsible for the operation of this device or its compliance with safety and regulatory standards. Please note that the use of this accessory with iPod, iPhone, iPad or Apple Watch may affect wireless performance. Google Play Store, Android and Fast Pair are trademarks of Google, LLC.

©2026 Starkey Laboratories, Inc. All Rights Reserved. P00008880 7/26 MISC5919-06-EN-ST